



## DK50 2x2V/110

For four dental units  
 Pour quatre unités dentaires  
 Para cuatro unidades dentales



3-4\*

Accessories/ Accessoires/ Accesorios: **BOX MD KJF FS REG AOK**

	DK50 2x2V/110	DK50 2x2V/110/M	DK50 2x2V/110S	DK50 2x2V/110S/M
	4	3 - 4	4	3 - 4
	-	✓	-	✓
	-	-	✓	✓
	280 l.min <sup>-1</sup> / 5bar	225 l.min <sup>-1</sup> / 5bar	280 l.min <sup>-1</sup> / 5bar	225 l.min <sup>-1</sup> / 5bar
	270 l.min <sup>-1</sup> / 6bar	215 l.min <sup>-1</sup> / 6bar	270 l.min <sup>-1</sup> / 6bar	215 l.min <sup>-1</sup> / 6bar
	210 l.min <sup>-1</sup> / 8bar	165 l.min <sup>-1</sup> / 8bar	210 l.min <sup>-1</sup> / 8bar	165 l.min <sup>-1</sup> / 8bar
S1-S3	S1 - 100%	S1 - 100%	S1 - 100%	S1 - 100%
	≤ 73 dB(A)	≤ 73 dB(A)	≤ 55 dB(A)	≤ 56 dB(A)

\* Number of dental units is subject to regional requirements.  
 \* Le nombre d'unités dentaires dépend des exigences régionales.  
 \* El número de unidades dentales está sujeto a los requisitos regionales.

## DK50 2x4VR/110/M

For central air distribution  
 Pour la distribution d'air centralisée  
 Para distribución centralizada del aire



8+\*

Accessories/ Accessoires/ Accesorios: **BOX MD KJF FS REG AOK**

	DK50 2x4VR/110/M	DK50 2x4VR/110S/M
	8+	8+
	✓	✓
	-	✓
	430 l.min <sup>-1</sup> / 6bar	430 l.min <sup>-1</sup> / 6bar
	330 l.min <sup>-1</sup> / 8bar	330 l.min <sup>-1</sup> / 8bar
S1-S3	S1 - 100%	S1 - 100%
	≤ 77	≤ 58

\* Number of units depends on air demand of each unit.  
 \* Le nombre d'unités dépend de la demande en air de chaque unité.  
 \* El número de unidades depende de la demanda de aire de cada unidad.